




RoHS


包装图



干燥剂



胶带ADHESIVE TAPE



Note注解:

1. Put Housing in a PE bag, Packing detail see the table below

将 Housing放入PE袋内, 并放入一包干燥剂, 并将PE袋封好. 贴上标签.

2. Put PE bag packed products in cartons, Packing detail see the table below

将装好产品的PE袋放入纸箱内, 详细包装见下表

3. Label depends on customer request, carton opening joint with transparent tape

标签依客户要求而定, 纸箱开口处用透明胶带贴合.



Poles	Bag PCS
2*02	1000
2*03	1000
2*04	1000
2*05	1000
2*06	1000
2*07	1000
2*08	1000
2*09	1000
2*10	1000
2*11	1000
2*12	1000
2*13	1000
2*14	1000
2*15	1000
2*16	1000

DATE	REV	ECN NO.	DESCRIPTION	MODIFY	APPROVAL

GENERAL TOLERANCE

.X ±0.35

.XX ±0.25

.XXX ±0.15

X° ±0.2°

东莞市国亚电子有限公司
Dong Guan Guo Ya Connectors co., Ltd.

APPROVAL

Yangzhengguo

CHECK

Yangjinyi

DRAWN

Lviansheng

DATE

2014/12/02

PART NO.

A2541H-XXX


TITLE:

2.54mm Housing Package

UNIT	SCALE	SHEET	REV	NUMBER
mm	1:1	1/1	A	-039

RoHS

包装图



Note 注解:

1. Quantity 数量:

15K PCS/REEL 一卷15K/PCS

11 REEL/BOX 一箱11 卷

165K PCS/BOX 一箱165K/PCS

2. Each reel and outer box must be labeled and Eco-Label Respectively labeled

每盘和外箱都必须有标签及环保标签分别标示

3. Terminal winding direction as shown



端子缠绕方向如左图所示

4. There shall be no dirt such as deformation phenomenon, Mantissa box fillers must be used

每箱不可有脏污, 变形现象, 尾数箱必须用填充物

5. Carton material: K=K, Carton thickness: 6±1mm

纸箱材质: K=K, 纸箱厚度: 6±1mm



A							GENERAL TOLERANCE		GYA Connectors 东莞市国亚电子有限公司 Dong Guan Guo Ya Connectors co., Ltd.				PART NO. A2541T-XXX				
							.X ±0.35	TITLE: 2.54 mm Terminal Packing									
							.XX ±0.25										
								.XXX ±0.15	APPROVAL	CHECK	DRAWN	DATE	UNIT	SCALE	SHEET	REV	NUMBER
								X° ±0.2°					mm	1:1	1/1	A	-035
	DATE	REV	ECN NO.	DESCRIPTION	MODIFY	APPROVAL		Yangzhengguo	Yangjinyi	Lvliansheng	2014/12/02						